

Wire Tong Band For 2 in Pole

By Chance Lineman Tools & Equipment
Catalog # [M1729](#)

Wire Tongs have many applications for moving and holding live conductors clear of the working area, for flat crossarm and/or ridge pin-construction, on horizontal post insulator structures, all types of suspension insulator lines, as auxiliary arm braces, and in EHV construction for brace pole or ladder positioning guides. A whole family of clamps, attachments, saddles and lever lifts allow the wire tongs to be adapted specifically to the mechanical requirements of various maintenance jobs.

Features

- Two screws clamp band to wire tong
- Each screw is threaded into half of the band and engages a slot in opposite half
- This permits halves of the band to be separated by a sliding action without removing screws
- Hinge ring slides on band, allowing rotation of wire tong when tong is supported by rope blocks
- For positive insulation between rope blocks and live conductors, install band at least the minimum distance for voltage class

General

Diameter - Pole	2 in
Diameter - Pole Metric	50.8 mm
EU RoHS Indicator	No
Style	Band; 2" (51 mm)
Type	Wire Tong
UPC	096359043683

Dimensions

Dimensions	7.5 in x 2.375 in x 3.5 in
Dimensions Metric	19.1 mm x 6.0 mm x 8.9 mm
Height	3.5 in
Height Metric	8.9 mm
Length	7.5 in
Length Metric	19.1 mm
Weight	1.62 lb
WeightMetric	0.7 kg
Width	2.375 in
WidthMetric	6 mm

Product Assets





A Hubbell brand