

Saddle Wheel Tightner and Clevis

By Chance Lineman Tools & Equipment
Catalog # [M474015W](#)

WIRETONG SADDLE - W/ WIRETONG CLEVIS, Pole Type Wire Tong Saddles are made of lightweight aluminum for handling ease. These rugged heat-treated saddles will support a maximum of 1000 pounds (450kg) without the extension. The clamp is set far enough away from the base to give ample clearance for most jobs. Where additional clearance is required, the Wire Tong Saddle Extension can be easily bolted to the saddle. This heattreated aluminum-alloy extension is 4 inches (100mm) long and has a tested working load rating of 800 pounds (360kg). The Wheel Type fasteners are easy to apply, hold the saddle firmly in place, and prevent riding down and excessive play. The Wheel Tightener has the advantage of being able to fit into close places such as between crossarm braces, under guy wires, etc.



General

EU RoHS Indicator	No
Style	Pole Saddle & Tightener w/ Clevis
Type	Wire Tong
UPC	096359048060

Dimensions

Dimensions	15.75 in x 10 in x 5.375 in
Dimensions Metric	40.0 mm x 25.4 mm x 13.7 mm
Height	5.375 in
Height Metric	13.7 mm
Length	15.75 in
Length Metric	40 mm
Weight	7 lb
WeightMetric	3.2 kg
Width	10 in
WidthMetric	25.4 mm

Product Assets

[Sales Drawings - SA_M4740-3W](#)