



## Pole Clamp Only, 2 in

By Chance Lineman Tools & Equipment  
Catalog # [M47412](#)

Pole Type Wire Tong Saddles are made of lightweight aluminum for handling ease. These rugged heat-treated saddles will support a maximum of 1000 pounds (450kg) without the extension. The clamp is set far enough away from the base to give ample clearance for most jobs. Where additional clearance is required, the Wire Tong Saddle Extension can be easily bolted to the saddle. This heat-treated aluminum-alloy extension is 4 inches (100mm) long and has a tested working load rating of 800 pounds (360kg). The Wheel Type fasteners are easy to apply, hold the saddle firmly in place, and prevent riding down and excessive play. The Wheel Tightener has the advantage of being able to fit into close places such as between crossarm braces, under guy wires, etc.



### General

|       |                 |
|-------|-----------------|
| Style | Pole Clamp Only |
| Type  | Wire Tong       |
| UPC   | 096359048190    |

### Dimensions

|                   |                             |
|-------------------|-----------------------------|
| Dimensions        | 6.25 in x 5.56 in x 5.5 in  |
| Dimensions Metric | 15.9 mm x 14.1 mm x 14.0 mm |
| Height            | 5.5 in                      |
| Height Metric     | 14 mm                       |
| Length            | 6.25 in                     |
| Length Metric     | 15.9 mm                     |
| Weight            | 2 lb                        |
| WeightMetric      | 0.9 kg                      |
| Width             | 5.56 in                     |
| WidthMetric       | 14.1 mm                     |

### Logistics

|                 |     |
|-----------------|-----|
| Pallet Quantity | 343 |
|-----------------|-----|

### Product Assets

[Sales Drawings - SA\\_M4740-3W](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-M47412-SPEC-EN | REV 6/2024