

Pole Clamp Only, 3 in

By Chance Lineman Tools & Equipment
Catalog # [M47415](#)

POLE CLAMP - 3IN, Pole Type Wire Tong Saddles are made of lightweight aluminum for handling ease. These rugged heat-treated saddles will support a maximum of 1000 pounds (450kg) without the extension. The clamp is set far enough away from the base to give ample clearance for most jobs. Where additional clearance is required, the Wire Tong Saddle Extension can be easily bolted to the saddle. This heat-treated aluminum-alloy extension is 4 inches (100mm) long and has a tested working load rating of 800 pounds (360kg). The Wheel Type fasteners are easy to apply, hold the saddle firmly in place, and prevent riding down and excessive play. The Wheel Tightener has the advantage of being able to fit into close places such as between crossarm braces, under guy wires, etc.



*Representative Image

General

EU RoHS Indicator	No
Style	Pole Clamp Only
Type	Wire Tong
UPC	096359048213

Dimensions

Dimensions	9.5 in x 5 in x 6.25 in
Dimensions Metric	24.1 mm x 12.7 mm x 15.9 mm
Height	6.25 in
Height Metric	15.9 mm
Length	9.5 in
Length Metric	24.1 mm
Weight	2.16 lb
WeightMetric	1 kg
Width	5 in
WidthMetric	12.7 mm

Product Assets

[Sales Drawings - SA_M4740-3W](#)