

Fixed Pole Mount for Platforms

By Chance Lineman Tools & Equipment
Catalog # [M490110W](#)

Includes one 30 in (.76 m) Chain Binder with self-locking handwheel, and one hinge pin



Features

Fits all Chance platforms except Suspension model

General

| | |
|-------------------|-----------------------------|
| EU RoHS Indicator | No |
| Style | Fixed Pole Mount Attachment |
| UPC | 096359048381 |

Dimensions

| | |
|-------------------|-----------------------------|
| Dimensions | 13 in x 13 in x 14 in |
| Dimensions Metric | 33.0 mm x 33.0 mm x 35.6 mm |
| Height | 14 in |
| Height Metric | 35.6 mm |
| Length | 13 in |
| Length Metric | 33 mm |
| Weight | 12 lb |
| WeightMetric | 5.4 kg |
| Width | 13 in |
| WidthMetric | 33 mm |

Product Assets

[Installation Manuals - Instructions for CHANCE® Temporary Work Platform](#)

[Installation Manuals - CHANCE® Tools Manuals](#)

[Sales Drawings - SA_M490110W](#)