



LoadLocker Ammeter Up to 400kV 60 Hz

By Chance Lineman Tools & Equipment
Catalog # [MEAMP21RW](#)

U-shape jaw senses the amperage present between tines, wide jaw for up to 2000 Amps

Features

- Open-end design lets you check loads on components not accessible by other hot-line ammeters
- Universal fitting mounts on insulated hotsticks
- Single button operation
- HOLD feature lets you bring down single reading to eye level
- Auto shut off after five minutes idle, or manually turn off by depressing button for five seconds

General

Catalog Number	MEAMP21RW
EU RoHS Indicator	No
Style	LoadLocker Ammeter, Up to 400kV
UPC	096359241676

Dimensions

Jaw Width	3.8 in
Weight	3.1 lb
WeightMetric	1.4 kg



*Representative Image

Electrical Ratings

Amperage - Display Range	0-99.9 Amperes (0.1 Amp increments); 100-1999 Amperes (1.0 Amp increments)
Amperage Rating	Up to 2000 A
Withstand Voltage	Up to 400 kV

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Instruments and Meters](#)
- [Installation Manuals - CHANCE LoadLocker Ammeter Operator's Manual](#)
- [Specifications - MEAMP21RW](#)