

LoadLocker Ammeter Up to 500kV 60 Hz

By Chance Lineman Tools & Equipment
Catalog # [MEAMP32RN](#)

U-shape jaw senses the amperage present between tines, narrow jaw for up to 5000 Amps



*Representative Image

Features

- Open-end design lets you check loads on components not accessible by other hot-line ammeters
- Universal fitting mounts on insulated hotsticks
- Single button operation
- HOLD feature lets you bring down single reading to eye level
- Auto shut off after five minutes idle, or manually turn off by depressing button for five seconds

General

Duty	N/A
EU RoHS Indicator	No
UPC	096359466512

Dimensions

Jaw Width	2.5 in
Weight	3 lb
WeightMetric	1.3 kg

Electrical Ratings

Amperage - Display Range	0-99.9 Amperes (0.1 Amp increments); 100-1999 Amperes (1.0 Amp increments); 2000-5000 Amperes (0.01 kA increments)
Amperage Rating	Up to 5000 A
Withstand Voltage	Up to 500 kV

Product Assets

[Installation Manuals - CHANCE LoadLocker Ammeter Operator's Manual](#)