



# LoadLocker Ammeter Up to 500kV 50 Hz

By Chance Lineman Tools & Equipment

Catalog # [MEAMP32RN2](#)



U-shape jaw senses the amperage present between tines, narrow jaw for up to 5000 Amps

### Features

- Open-end design lets you check loads on components not accessible by other hot-line ammeters
- Universal fitting mounts on insulated hotsticks
- Single button operation
- HOLD feature lets you bring down single reading to eye level
- Auto shut off after five minutes idle, or manually turn off by depressing button for five seconds

### General

Catalog Number	MEAMP32RN2
Duty	N/A
UPC	096359570486

### Dimensions

Jaw Width	2.5 in
Weight	3 lb
WeightMetric	1.3 kg

### Electrical Ratings

Amperage - Display Range	0-99.9 Amperes (0.1 Amp increments); 100-1999 Amperes (1.0 Amp increments); 2000-5000 Amperes (0.01 kA increments)
Amperage Rating	Up to 5000 A
Withstand Voltage	Up to 500 kV

### Logistics

Carton Quantity	5
-----------------	---

### Product Assets

- [Catalogs - Instruments and Meters](#)
- [Installation Manuals - CHANCE LoadLocker Ammeter Operator's Manual](#)
- [Specifications - MEAMP32RN2](#)



A Hubbell brand