



# Straight Cuff Gloves Class 00 11" Black Size 7

By Chance Lineman Tools & Equipment  
Catalog # PSC0011B7



CLASS 00 11" BLACK SIZE 7

## Features

- Class 00
- Maximum use voltage 500 volts AC / 750 DC
- color is black

## General

Color	Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359447214

## Dimensions

Length	11 in
Weight	0.51 lb
Width	7 in

## Electrical Ratings

Voltage - Maximum	• 500 VAC
	• 750 VDC
Voltage Rating	Class 00 V

## Logistics

Carton Quantity	10
Pallet Quantity	120

## Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Literature - Low-Voltage Rubber Gloves \(SF09010E\)](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)
- [Video - CHANCE® - Low Voltage Rubber Gloves](#)



A proud member of the Hubbell Family.