



Straight Cuff Gloves Class 00 11" Yellow Size 7

By Chance Lineman Tools & Equipment
Catalog # [PSC0011Y7](#)



CLASS 00 11" YELLOW SIZE 7

Features

- Class 00
- Maximum use voltage 500 volts AC / 750 DC
- color is yellow

General

Color	Yellow
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359447306

Dimensions

Length	11 in
Weight	0.51 lb
Width	7 in

Electrical Ratings

Voltage - Maximum	500 VAC
	750 VDC
Voltage Rating	Class 00 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - Rubber Insulating Gloves](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Spanish](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions](#)
- [Literature - Low-Voltage Rubber Gloves](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field](#)
- [Video - CHANCE® - Low Voltage Rubber Gloves](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-PSC0011Y7-SPEC-EN | REV 6/2024