



Straight Cuff Gloves Class 00 14" Black Size 10

By Chance Lineman Tools & Equipment
Catalog # PSC0014B10



CLASS 00 14" BLACK SIZE 10

Features

- Class 00
- Maximum use voltage 500 volts AC / 750 DC
- color is black

General

Color	Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359449560

Dimensions

Length	14 in
Weight	0.74 lb
Width	10 in

Electrical Ratings

Voltage - Maximum	• 500 VAC
	• 750 VDC
Voltage Rating	Class 00 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Literature - Low-Voltage Rubber Gloves \(SF09010E\)](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)
- [Video - CHANCE® - Low Voltage Rubber Gloves](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC0014B10-SPEC-EN | REV 1/2024