



Straight Cuff Gloves Class 00 14" Black Size 8H

By Chance Lineman Tools & Equipment
Catalog # [PSC0014B8H](#)



CLASS 00 14" BLACK SIZE 8H

Features

- Class 00
- Maximum use voltage 500 volts AC / 750 DC
- color is black

General

Color	Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359447412

Dimensions

Length	14 in
Weight	0.71 lb
Width	8.5 in

Electrical Ratings

Voltage - Maximum	500 VAC 750 VDC
Voltage Rating	Class 00 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - Rubber Insulating Gloves](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Spanish](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions](#)
- [Literature - Low-Voltage Rubber Gloves](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field](#)
- [Video - CHANCE® - Low Voltage Rubber Gloves](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-PSC0014B8H-SPEC-EN | REV 6/2024