



Straight Cuff Gloves Class 0 11" Black Size 7

By Chance Lineman Tools & Equipment
Catalog # PSC011B7



CLASS 0 11" BLACK SIZE 7

Features

- Class 0
- Maximum use voltage 1,000 volts AC / 1,500 DC
- color is black

General

Color	Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359447559

Dimensions

Length	11 in
Weight	0.64 lb
Width	7 in

Electrical Ratings

Voltage - Maximum	• 1000 VAC
	• 1500 VDC
Voltage Rating	Class 0 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Literature - Low-Voltage Rubber Gloves \(SF09010E\)](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC011B7-SPEC-EN | REV 1/2024