



# Straight Cuff Gloves Class 1 16" Red/Blk Size 10H

By Chance Lineman Tools & Equipment  
Catalog # [PSC116RB10H](#)



CLASS 1 16" RED/BLK SIZE 10H

## Features

- Class 1
- Maximum use voltage 7,500 volts AC / 11,250 DC
- color is red under black

## General

Color	Red Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359448341

## Dimensions

Length	16 in
Weight	1.51 lb
Width	10.5 in

## Electrical Ratings

Voltage - Maximum	• 7500 VAC
	• 11250 VDC
Voltage Rating	Class 1 V

## Logistics

Carton Quantity	10
Pallet Quantity	120

## Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-PSC116RB10H-SPEC-EN | REV 1/2024