



Bell Cuff Gloves Class 2 14" Red/Blk Size 9H

By Chance Lineman Tools & Equipment
Catalog # PSC214BCRB9H

BELL CLASS 2 14" RED/BLK SIZE 9H



Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 volts DC
- color is red under black

General

Color	Red Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Bell Cuff
UPC	096359457091

Dimensions

Length	14 in
Weight	1.64 lb
Width	9.5 in

Electrical Ratings

Voltage - Maximum	• 17000 VAC
	• 25500 VDC
Voltage Rating	Class 2 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

[Catalogs - Rubber Insulating Gloves \(2650\)](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
[Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC214BCRB9H-SPEC-EN | REV 1/2024