



Bell Cuff Gloves Class 2 14" Yel/Blk Size 10

By Chance Lineman Tools & Equipment
Catalog # [PSC214BCYB10](#)



BELL CLASS 2 14" YEL/BLK SIZE 10

Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 volts DC
- color is yellow under black

General

Color	Yellow Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Bell Cuff
UPC	096359457046

Dimensions

Length	14 in
Weight	1.73 lb
Width	10 in

Electrical Ratings

Voltage - Maximum	• 17000 VAC
	• 25500 VDC
Voltage Rating	Class 2 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.