



Bell Cuff Gloves Class 2 14" Yel/Blk Size 9

By Chance Lineman Tools & Equipment
Catalog # [PSC214BCYB9](#)



BELL CLASS 2 14" YEL/BLK SIZE 9

Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 volts DC
- color is yellow under black

General

Color	Yellow Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Bell Cuff
UPC	096359457022

Dimensions

Length	14 in
Weight	1.56 lb
Width	9 in

Electrical Ratings

Voltage - Maximum	• 17000 VAC
	• 25500 VDC
Voltage Rating	Class 2 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC214BCYB9-SPEC-EN | REV 1/2024