

Straight Cuff Gloves Class 2 14" Red/Blk Size 8H

By Chance Lineman Tools & Equipment
Catalog # [PSC214RB8H](#)



CLASS 2 14" RED/BLK SIZE 8H

Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 DC
- color is red under black

General

Color	Red Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359448549

Dimensions

Length	14 in
Weight	1.35 lb
Width	8.5 in

Electrical Ratings

Voltage - Maximum	17000 VAC 25500 VDC
Voltage Rating	Class 2 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

[Catalogs - Rubber Insulating Gloves](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Portuguese](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Spanish](#)
[Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field](#)



A Hubbell brand