

## Straight Cuff Gloves Class 2 14" Yel/Blk Size 8

By Chance Lineman Tools & Equipment  
Catalog # [PSC214YB8](#)



CLASS 2 14" YEL/BLK SIZE 8

### Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 DC
- color is yellow under black

### General

|                   |                    |
|-------------------|--------------------|
| Color             | Yellow Under Black |
| EU RoHS Indicator | No                 |
| Material          | Natural Rubber     |
| Style             | Straight Cuff      |
| UPC               | 096359448457       |

### Dimensions

|        |         |
|--------|---------|
| Length | 14 in   |
| Weight | 1.33 lb |
| Width  | 8 in    |

### Electrical Ratings

|                   |                        |
|-------------------|------------------------|
| Voltage - Maximum | 17000 VAC<br>25500 VDC |
| Voltage Rating    | Class 2 V              |

### Logistics

|                 |     |
|-----------------|-----|
| Carton Quantity | 10  |
| Pallet Quantity | 120 |

### Product Assets

[Catalogs - Rubber Insulating Gloves](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Portuguese](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Spanish](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions](#)  
[Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field](#)



A Hubbell brand