



Straight Cuff Gloves Class 2 14" Yel/Blk Size 9H

By Chance Lineman Tools & Equipment
Catalog # [PSC214YB9H](#)



CLASS 2 14" YEL/BLK SIZE 9H

Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 DC
- color is yellow under black

General

Color	Yellow Under Black
Material	Natural Rubber
Style	Straight Cuff
UPC	096359448488

Dimensions

Length	14 in
Weight	1.54 lb
Width	9.5 in

Electrical Ratings

Voltage - Maximum	• 17000 VAC
	• 25500 VDC
Voltage Rating	Class 2 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC214YB9H-SPEC-EN | REV 1/2024