



Straight Cuff Gloves Class 2 16" Black Size 10H

By Chance Lineman Tools & Equipment
Catalog # PSC216B10H



CLASS 2 16" BLACK SIZE 10H

Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 DC
- color is black

General

| | |
|-------------------|----------------|
| Color | Black |
| EU RoHS Indicator | No |
| Material | Natural Rubber |
| Style | Straight Cuff |
| UPC | 096359448662 |

Dimensions

| | |
|--------|---------|
| Length | 16 in |
| Weight | 1.97 lb |
| Width | 10.5 in |

Electrical Ratings

| | |
|-------------------|-------------|
| Voltage - Maximum | • 17000 VAC |
| | • 25500 VDC |
| Voltage Rating | Class 2 V |

Logistics

| | |
|-----------------|-----|
| Carton Quantity | 10 |
| Pallet Quantity | 120 |

Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.