



Bell Cuff Gloves Class 2, 16 in Yel/Blk Size 10H

By Chance Lineman Tools & Equipment
Catalog # [PSC216BCYB10H](#)



BELL CLASS 2 16" YEL/BLK SIZE 10H

Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 volts DC
- color is yellow under black

General

Catalog Number	PSC216BCYB10H
Color	Yellow Under Black
Material	Natural Rubber
Size	10.5
Style	Bell Cuff
UPC	096359457176

Dimensions

Length	16 in
Weight	2 lb
Width	10.5 in

Electrical Ratings

Voltage - Maximum	• 17000 VAC • 25500 VDC
Voltage Rating	Class 2 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - Rubber Insulating Gloves](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Spanish](#)
- [Specifications - PSC216BCYB10H](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field](#)