



# Contour Cuff Gloves Class 2, 18 Red/Blk Size 10

By Chance Lineman Tools & Equipment  
Catalog # [PSC218CRB10](#)



CONTOUR CLASS 2, 18 RED/BLK SZ 10

## Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 volts DC
- color is red under black

## General

Color	Red Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Contour Cuff
UPC	096359487265

## Dimensions

Length	18 in
Weight	2 lb
Width	10 in

## Electrical Ratings

Voltage - Maximum	• 17000 VAC
	• 25500 VDC
Voltage Rating	Class 2 V

## Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-PSC218CRB10-SPEC-EN | REV 1/2024