



CHANCE® Contour Cuff Gloves Class 2, 18 Yel/Blk Size 10

By Chance Lineman Tools & Equipment
Catalog # PSC218CYB10



CHANCE® CONTOUR CLASS 2, 18 YEL/BLK SZ 10

Features

- Class 2
- Maximum use voltage 17,000 volts AC / 25,500 volts DC
- color is yellow under black

General

Color	Yellow Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Contour Cuff
UPC	096359487340

Dimensions

Length	18 in
Weight	3 lb
Width	10 in

Electrical Ratings

Voltage - Maximum	• 17000 VAC
	• 25500 VDC
Voltage Rating	Class 2 V

Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CLTE-PSC218CYB10-SPEC-EN | REV 8/2023