

Class 2, Type II Flexible Rubber Cutout Cover

By Chance Lineman Tools & Equipment
Catalog # [PSC24CC](#)

Meets or exceeds ASTM Standard Specification D1048. Class 2 Type II (ozone-resistant). Protection from accidental brush contact with energized components during line maintenance. Made of ozone/corona-resistant elastomer. Special formulation exhibits superior resistance to long-term aging/checking. Standard package quantity is 28. Twenty-two by twenty-two inches, and 12 eyelets.

Features

- For use on Overhead Cutouts
- Conforms to ASTM D1049
- Dimensions of 24" x 15" x 3.75"

General

Catalog Number	PSC24CC
Style	Flexible Rubber
UPC	096359584094

Dimensions

Length	288 in
--------	--------



Weight	7 lb
WeightMetric	3.1 kg

Electrical Ratings

Voltage - Maximum	17 kV
Voltage Rating	Class 2 V

Product Assets

- [Literature - Cutout Gloves](#)
- [Literature - Cover-Up Care](#)
- [Sales Drawings - SAPSC24CC](#)
- [Specifications - PSC24CC](#)