



## Bell Cuff Gloves Class 3 16" Yel/Blk Size 10H

By Chance Lineman Tools & Equipment  
Catalog # PSC316BCYB10H

BELL CLASS 3 16" YEL/BLK SIZE 10H



### Features

- Class 3
- Maximum use voltage 26,500 volts AC / 39,750 volts DC
- color is yellow under black

### General

Color	Yellow Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Bell Cuff
UPC	096359457411

### Dimensions

Length	16 in
Weight	2.5 lb
Width	10.5 in

### Electrical Ratings

Voltage - Maximum	• 26500 VAC
	• 39750 VDC
Voltage Rating	Class 3 V

### Logistics

Carton Quantity	10
Pallet Quantity	120

### Product Assets

[Catalogs - Rubber Insulating Gloves \(2650\)](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)  
[Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-PSC316BCYB10H-SPEC-EN | REV 1/2024