



Straight Cuff Gloves Class 3, 16 in Red/Blk Size 10

By Chance Lineman Tools & Equipment
Catalog # [PSC316RB10](#)



CLASS 3 16" RED/BLK SIZE 10

Features

- Class 3
- Maximum use voltage 26,500 volts AC / 39,750 DC
- color is red under black

General

Catalog Number	PSC316RB10
Color	Red Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Size	10
Style	Straight Cuff
UPC	096359449119

Dimensions

Length	16 in
Weight	2.13 lb
Width	10 in

Electrical Ratings

Voltage - Maximum	• 26500 VAC • 39750 VDC
-------------------	---

Voltage Rating	Class 3 V
----------------	-----------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - Rubber Insulating Gloves](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Spanish](#)
- [Specifications - PSC316RB10](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field](#)