



# Straight Cuff Gloves Class 3 16" Yel/Blk Size 8

By Chance Lineman Tools & Equipment  
Catalog # PSC316YB8



CLASS 3 16" YEL/BLK SIZE 8

## Features

- Class 3
- Maximum use voltage 26,500 volts AC / 39,750 DC
- color is yellow under black

## General

Color	Yellow Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359448990

## Dimensions

Length	16 in
Weight	1.88 lb
Width	8 in

## Electrical Ratings

Voltage - Maximum	• 26500 VAC
	• 39750 VDC
Voltage Rating	Class 3 V

## Logistics

Carton Quantity	10
Pallet Quantity	120

## Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-PSC316YB8-SPEC-EN | REV 1/2024