



Contour Cuff Gloves Class 3, 18 Red/Blk Size 10H

By Chance Lineman Tools & Equipment
Catalog # [PSC318CRB10H](#)

CONTOUR CLASS 3, 18 RED/BLK SZ 10H



Features

- Class 3
- Maximum use voltage 26,500 volts AC / 39,750 volts DC
- color is red under black

General

Color	Red Under Black
Material	Natural Rubber
Style	Contour Cuff
UPC	096359487487

Dimensions

Length	18 in
Weight	3 lb
Width	10.5 in

Electrical Ratings

Voltage - Maximum	• 26500 VAC
	• 39750 VDC
Voltage Rating	Class 3 V

Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC318CRB10H-SPEC-EN | REV 1/2024