



Contour Cuff Gloves Class 3, 18 Red/Blk Size 12

By Chance Lineman Tools & Equipment
Catalog # [PSC318CRB12](#)

CONTOUR CLASS 3, 18 RED/BLK SZ 12



Features

- Class 3
- Maximum use voltage 26,500 volts AC / 39,750 volts DC
- color is red under black

General

Color	Red Under Black
Material	Natural Rubber
Style	Contour Cuff
UPC	096359487500

Dimensions

Length	18 in
Weight	3.5 lb
Width	12 in

Electrical Ratings

Voltage - Maximum	• 26500 VAC
	• 39750 VDC
Voltage Rating	Class 3 V

Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC318CRB12-SPEC-EN | REV 1/2024