

## Straight Cuff Gloves Class 3 18" Yel/Blk Size 12

By Chance Lineman Tools & Equipment  
Catalog # [PSC318YB12](#)



CLASS 3 18" YEL/BLK SIZE 12

### Features

- Class 3
- Maximum use voltage 26,500 volts AC / 39,750 DC
- color is yellow under black

### General

Color	Yellow Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359449225

### Dimensions

Length	18 in
Weight	2.33 lb
Width	12 in

### Electrical Ratings

Voltage - Maximum	26500 VAC 39750 VDC
Voltage Rating	Class 3 V

### Logistics

Carton Quantity	10
Pallet Quantity	120

### Product Assets

[Catalogs - Rubber Insulating Gloves](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Portuguese](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)  
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions Spanish](#)  
[Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field](#)



A Hubbell brand