

Fixed Strain Pole, 113 in (2.8 m), Clevis to Clevis

By Chance Lineman Tools & Equipment

Catalog # [PSC4002915](#)



Pole, Strain 113" with Clevis to Clevis

*Representative Image

Features

- Tested per OSHA & ASTM F711
- Accommodate a wide range of yoke plate designs and hole spacings
- Strain Poles made of 2 in (63 mm) diameter Epoxiglas®
- 12,000 lb. (5,443 kg) Working load limit with a 1 in (25 mm) wide clevis for aluminum conductor yoke plates

General

Catalog Number	PSC4002915
UPC	096359836223
Working Load Limit	12,000 lb
Working Load Limit Metric	5,443 kg

Dimensions

Dimension - L Length Overall	2,870 mm
mm	
Dimension - Length Overall	113 in
inch	
Weight	25.1 lb
WeightMetric	11.3 kg
Width	6.3 in

Product Assets

[Literature - Transmission Project Tools and Equipment Checklist](#)
[Specifications - PSC4002915](#)