



Fixed Strain Pole, 134 in (3.4 m), Clevis to Clevis

By Chance Lineman Tools & Equipment
Catalog # PSC4002916

Pole, Strain 113" with Clevis to Clevis



*Representative Image

Features

- Working length 113"
- Max load 12,000 lb

General

UPC	096359488972
Working Load Limit	12,000 lb
Working Load Limit Metric	5,443 kg

Dimensions

Dimension - L Length Overall mm	3,403 mm
Dimension - Length Overall inch	134 in
Dimensions	142 in x 6.375 in x 5.75 in
Height	5.75 in
Length	142 in
Length Metric	360.7 mm
Weight	27.0 lb
WeightMetric	12.2 kg
Width	6.375 in

Product Assets

[Catalogs - Tools and Grounding Catalog Full](#)
[Installation Manuals - CHANCE® Tools Manuals \(CENT_LTE_IOM_EN_00158\)](#)<LineBreak/>
[Literature - Transmission Project Tools and Equipment Checklist \(CENT_LTE_FRM_EN_00082\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC4002916-SPEC-EN | REV 1/2024