

Crossarm Link Stick - 1,500 lb. (680 kg) Working Load Limit

By Chance Lineman Tools & Equipment
Catalog # [PSC4004132](#)



The Crossarm Link Stick provides a 1,500 lb. working load limit. It hooks over a dead-end crossarm (up to 3.75 in x 4.75 in) on one end and provides a butt swivel on the other end that allows for connection with a hoist for the purpose of providing quick set-up for tension relief to a dead-end insulator or other component. No hassles connecting a sling.

Features

- 1-1/4"-diameter Epoxiglas™ pole with 21-1/2" insulating length
- Plastisol-coated 3/4"-diameter steel hook
- Hook's 5" opening fits standard 3-3/4" x 4-3/4" crossarms
- Galvanized-steel swivel eye on pole end for easy alignment
- Lifting eye on hook fitting for positioning by a hot line tool
- Rated working load: 1,500 lb. and 3,500 lb.

General

Catalog Number	PSC4004132
Color	Gray
Max Load Lbs.	1500 lb
Style	Crossarm Link Stick
Swivel Top?	Yes
UPC	096359575818
Working Load Limit	1,500 lb
Working Load Limit Metric	680 kg

Dimensions

Dimensions	21.5 in x 5 in x 5 in
Dimensions Metric	546 mm x 12.7 mm x 12.7 mm
Height	5 in
Height Metric	12.7 mm
Length	21.5 in
Length Metric	546 mm
Weight	8 lb
WeightMetric	3.6 kg
Width	5 in
WidthMetric	12.7 mm

Product Assets

[Catalogs - Load Handling Accessories](#)
[Installation Manuals - CHANCE® Tools Manuals](#)
[Specifications - PSC4004132](#)