



Crossarm Link Stick - 3,500 lb. (1,587 kg) Working Load Limit

By Chance Lineman Tools & Equipment
Catalog # [PSC4004372](#)



The Crossarm Link Stick provides a 3,500 lb. working load limit. It hooks over a dead-end crossarm (up to 3.75 in x 4.75 in) on one end and provides a butt swivel on the other end that allows for connection with a hoist for the purpose of providing quick set-up for tension relief to a dead-end insulator or other component. No hassles connecting a sling.

Features

- Quick and easy set up, no sling necessary
- Plastisol-coated steel hook
- Fits standard 3-3/4" x 4-3/4" crossarms with 5" hook
- Galvanized steel swivel eye on conductor end for easy alignment
- Lifting eye on hook fitting for easy positioning by a hot line tool
- Also available with 3500 lb-rated working load
- Insulated Epoxiglas™ length: 21.5"
- total length: 41"
- Custom Epoxiglas lengths available

General

Color	Black
Max Load Lbs.	3500 lb
Style	Crossarm Link Stick
UPC	096359635406
Working Load Limit	3,500 lb
Working Load Limit Metric	1,587 kg

Dimensions

Dimensions	21.5 in x 9 in x 9 in
Dimensions Metric	546 mm x 22.9 mm x 22.9 mm
Height	9 in
Height Metric	22.9 mm
Length	21.5 in
Length Metric	546 mm
Weight	10 lb
WeightMetric	4.5 kg
Width	9 in
WidthMetric	22.9 mm

Product Assets

[Catalogs - Load Handling Accessories](#)
[Installation Manuals - CHANCE® Tools Manuals](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-PSC4004372-SPEC-EN | REV 6/2024