

## Crossarm Link Stick - 3,500 lb. (1,587 kg) Working Load Limit

By Chance Lineman Tools & Equipment  
Catalog # [PSC4004372](#)



The Crossarm Link Stick provides a 3,500 lb. working load limit. It hooks over a dead-end crossarm (up to 3.75 in x 4.75 in) on one end and provides a butt swivel on the other end that allows for connection with a hoist for the purpose of providing quick set-up for tension relief to a dead-end insulator or other component. No hassles connecting a sling.

### Features

- Quick and easy set up, no sling necessary
- Plastisol-coated steel hook
- Fits standard 3-3/4" x 4-3/4" crossarms with 5" hook
- Galvanized steel swivel eye on conductor end for easy alignment
- Lifting eye on hook fitting for easy positioning by a hot line tool
- Also available with 3500 lb-rated working load
- Insulated Epoxiglas™ length: 21.5"
- total length: 41"
- Custom Epoxiglas lengths available

### General

Catalog Number	PSC4004372
Color	Black
Max Load Lbs.	3500 lb
Style	Crossarm Link Stick
UPC	096359635406

Working Load Limit	3,500 lb
Working Load Limit Metric	1,587 kg

### Dimensions

Dimensions	21.5 in x 9 in x 9 in
Dimensions Metric	546 mm x 22.9 mm x 22.9 mm
Height	9 in
Height Metric	22.9 mm
Length	21.5 in
Length Metric	546 mm
Weight	10 lb
WeightMetric	4.5 kg
Width	9 in
WidthMetric	22.9 mm

### Product Assets

[Catalogs - Load Handling Accessories](#)  
[Installation Manuals - CHANCE® Tools Manuals](#)  
[Specifications - PSC4004372](#)