

All-Angle Cog Wrench, 12 ft

By Chance Lineman Tools & Equipment
Catalog # [PSC4030187](#)

Controls on the All-Angle Cog Wrench permit operator efficiency in locating the wrench on energized hardware



*Representative Image

Features

- Tested per OSHA & ASTM F711
- 15 ft-lb maximum torque rating
- Controls permit operator efficiency in locating the wrench on energized hardware
- Handgrip steadies tool and holds cog housing in place while pole is rotated, turning cogs to engage wrench on the nut or bolt
- Wrench head angle in relation to handle is adjustable within a range of 140°
- Wing nuts on either side of head tightens to hold head in position during use
- Chance Epoxiglas™ Hot Line Tool is 1-1/2" in diameter with 3/8" diameter fiberglass control rod
- Aluminum alloy handgrip, bronze alloy cog housing, and hardened steel gears

General

| | |
|----------------|--------------|
| Catalog Number | PSC4030187 |
| UPC | 096359533092 |

Dimensions

| | |
|--------------|-------|
| Length | 12 ft |
| Weight | 9 lb |
| WeightMetric | 4 kg |

Product Assets

[Catalogs - Tools and Grounding Catalog Full](#)
[Catalogs - Insulated Hand Tools](#)
[Installation Manuals - CHANCE® Tools Manuals](#)
[Specifications - PSC4030187](#)