



MULTI-RANGE VOLT DET (MRVD), 16-161KV TP

By Chance Lineman Tools & Equipment
Catalog # [PSC4031029004](#)



A field intensity meter calibrated to read approximate line-to-line voltage when connected to any phase conductor

*Representative Image

Features

- Helps confirm a line is de-energized prior to performing maintenance
- Reads field intensity for approximate line-to-line voltage
- Capable of distinguishing actual line voltage from static or feedover from an adjacent line
- Must mount on proper length hotstick for the voltage class involved
- Pushbutton to confirm operational condition before and after each use

General

UPC 096359707561

Dimensions

Weight 8.25 lb

Logistics

Standard Package 1

Product Assets

[Catalogs - Instruments and Meters \(2450\)](#)
[Installation Manuals - CHANCE Multi-Range Voltage Detectors \(MRVD\) Operating Instructions \(P403-2229\)](#)

Related Products

[H18766S - Shepherd Hook Probe](#)
[H18765 - Angle Probe](#)
[H18766P - Pigtail Hook Probe](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC4031029004-SPEC-EN | REV 1/2024