

Multi-Range Voltage Indicator (MRVI) 1 to 80kV

By Chance Lineman Tools & Equipment
Catalog # [PSC4033710](#)



The Multi-Range Voltage Indicator® is a portable tool to confirm that an AC (Alternating Current) high voltage circuit is energized or de-energized prior to performing maintenance.

Features

- Helps confirm a line is energized or de-energized
- Field intensity determines approximate Phase-to-Phase and Phase-to-Ground voltage
- Easily read dial face with brightly illuminated pointer indicate voltage
- Bluetooth technology allows live display on free Android/IOS mobile app
- Lightweight design with belt clip storage bag

General

UPC 096359643418

Dimensions

Weight 1.25 lb
WeightMetric 0.5 kg

Logistics

Standard Package 1

Product Assets

[Installation Manuals - CHANCE® Voltage Indicator Tester](#)
[Operating Instructions - PSC4033582](#)
[Installation Manuals - CHANCE® Multi-Range Voltage Indicator](#)
[Operating Instructions - PSC4033710](#)
[Literature - Multi-Range Voltage Indicator \(MRVI\)](#)
[Literature - Next Generation CHANCE Voltage Indicators](#)
[Literature - AD09154E Powerlineman New Meters](#)
[Sales Drawings - Sales Drawing \(PSC4033710\)](#)
[Video - CHANCE Multi-Range Voltage Indicator](#)