



Class 2, Temporary Conductor Cover, 5 ft.

By Chance Lineman Tools & Equipment
Catalog # [PSC4060616](#)

Class 2, Temporary Conductor Cover, 5 ft.

Features

- Design tested to ASTM F712 Class 2
- Lightweight - Approximately 50% the weight of similar rubber hose
- Protects workers from accidental brush contact with energized components during line maintenance
- Made from bright orange polyethylene
- Maximum use voltage of 14.6kV covered-phase-to-covered-phase
- 5 foot overall length

General

Catalog Number	PSC4060616
Color - Jumper Insulation	Orange
Style	Rubber Glove Application
UPC	096359576273

Dimensions

Weight	1.9 lb
WeightMetric	0.8 kg

Electrical Ratings

Voltage Rating	Class 2 V
Withstand Voltage	15 kV Guarded Phase-to-Guarded Phase

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Cover-Up Equipment](#)
- [Literature - Cover-Up Care](#)
- [Sales Drawings - Temporary Conductor Cover, Class 2](#)
- [Specifications - PSC4060616](#)



A Hubbell brand