



Class 2, Temporary Conductor Cover, 6 ft.

By Chance Lineman Tools & Equipment
Catalog # [PSC4060617](#)



Class 2, Temporary Conductor Cover, 6 ft.

Features

- Design tested to ASTM F712 Class 2
- Lightweight - Approximately 50% the weight of similar rubber hose
- Protects workers from accidental brush contact with energized components during line maintenance
- High visibility orange color
- Maximum use voltage of 14.6kV covered-phase-to-covered-phase
- 6 foot overall length

General

Color - Jumper Insulation	Orange
Style	Rubber Glove Application
UPC	096359576280

Dimensions

Weight	2.3 lb
WeightMetric	1 kg

Electrical Ratings

Voltage Rating	Class 2 V
Withstand Voltage	15 kV Guarded Phase-to-Guarded Phase

Logistics

Carton Quantity	10
Pallet Quantity	210

Product Assets

[Literature - Cover-Up Care](#)
[Sales Drawings - Temporary Conductor Cover, Class 2](#)



A Hubbell brand