



Class 2, Type II Slotted Blanket, 22 in x 22 in with 12 Eyelets

By Chance Lineman Tools & Equipment
Catalog # PSC4060708

Meets or exceeds ASTM Standard Specification D1048. Class 2 Type II (ozone-resistant). Protection from accidental brush contact with energized components during line maintenance. Made of ozone/corona-resistant elastomer. Special formulation exhibits superior resistance to long-term aging/checking. Standard package quantity is 12. Twenty-two by twenty-two inches, 1.5 inch (38 mm) diameter center hole, and 12 eyelets.

Features

- Meets or exceeds ASTM Standard Specification D1048
- Class 2 Type II (ozone-resistant)
- Protection from accidental brush contact with energized components during line maintenance
- Made of ozone/corona-resistant elastomer
- Special formulation exhibits superior resistance to long-term aging/checking
- Standard package quantity is 12
- 1.5" (38 mm) diameter center hole
- 12 eyelets

General

Type Blankets
UPC 096359661962



Dimensions

Weight 3.0 lb
WeightMetric 1.3 kg

Product Assets

[Literature - Cover-Up Care \(BR09003E\)](#)
[Technical Solutions - CH-PSC4060708-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC4060708-SPEC-EN | REV 1/2024