



Bell Cuff Gloves Class 4 16" Yel/Blk Size 12

By Chance Lineman Tools & Equipment
Catalog # PSC416BCYB12



BELL CLASS 4 16" YEL/BLK SIZE 12

Features

- Class 4
- Maximum use voltage 36,000 volts AC / 54,000 volts DC
- color is yellow under black

General

Color	Yellow Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Bell Cuff
UPC	096359457671

Dimensions

Length	16 in
Weight	2.95 lb
Width	12 in

Electrical Ratings

Voltage - Maximum	• 36000 VAC
	• 54000 VDC
Voltage Rating	Class 4 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

- [Catalogs - Rubber Insulating Gloves \(2650\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
- [Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
- [Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC416BCYB12-SPEC-EN | REV 1/2024