



Straight Cuff Gloves Class 4 18" Red/Blk Size 10H

By Chance Lineman Tools & Equipment
Catalog # [PSC418RB10H](#)



CLASS 4 18" RED/BLK SIZE 10H

Features

- Class 4
- Maximum use voltage 36,000 volts AC / 54,000 DC
- color is red under black

General

Color	Red Under Black
EU RoHS Indicator	No
Material	Natural Rubber
Style	Straight Cuff
UPC	096359449522

Dimensions

Length	18 in
Weight	2.62 lb
Width	10.5 in

Electrical Ratings

Voltage - Maximum	• 36000 VAC
	• 54000 VDC
Voltage Rating	Class 4 V

Logistics

Carton Quantity	10
Pallet Quantity	120

Product Assets

[Catalogs - Rubber Insulating Gloves \(2650\)](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-fra\) French](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-por\) Portuguese](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-eng\)](#)
[Installation Manuals - CHANCE Rubber Insulating Gloves User Instructions \(07-1102-esp\) Spanish](#)
[Video - CHANCE Cleaning and Inspecting Rubber Gloves in the Field \(VI09014E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC418RB10H-SPEC-EN | REV 1/2024