



Long Stud, 30mm, 5H

By Chance Lineman Tools & Equipment
Catalog # [PSC6003492](#)

5H Long Ball Stud, 30mm ball, 3.0" x .75" dia. shaft, 5/8-11 UNC threads



Features

- Grade 5H Rated
- Rated 47kA with X/R = 30
- First cycle current peak = 127 kA
- Last cycle current peak = 70 kA
- Test duration = 15 cycles

General

UPC 096359567820

Dimensions

Weight 1.4 lb

Certifications and Compliance

Fault Current - ASTM Grade 5H

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)

[Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs \(CENT-LTE-H-RATED-GROUNDING-BR-EN-00301_web\)](#)

[Sales Drawings - SA6003492](#)

[Video - CHANCE Temporary Protective Grounding \(VI09071E0620\)](#)

[Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC6003492-SPEC-EN | REV 1/2024