



# Short Stud, 30mm, Female Threads, 5H

By Chance Lineman Tools & Equipment  
Catalog # [PSC6003493](#)

5H Short Ball Stud, 30mm ball, .8" x .75" dia. shaft, 5/8-11 UNC Female Threads



## Features

- Grade 5H Rated
- Rated 47kA with X/R = 30
- First cycle current peak = 127 kA
- Last cycle current peak = 70 kA
- Test duration = 15 cycles

## General

UPC 096359567400

## Dimensions

Weight 1.6 lb

## Certifications and Compliance

Fault Current - ASTM Grade 5H

## Logistics

Carton Quantity 25  
Pallet Quantity 1125

## Product Assets

- [Catalogs - Grounding Equipment \(3000\)](#)
- [Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs \(CENT-LTE-H-RATED-GROUNDING-BR-EN-00301\\_web\)](#)
- [Sales Drawings - SA6003493](#)
- [Technical Solutions - CH-PSC6003493-SPEC-EN](#)
- [Video - CHANCE Temporary Protective Grounding \(VI09071E0620\)](#)
- [Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-PSC6003493-SPEC-EN | REV 1/2024