

## All-Angle Ground Clamp, 5H

By Chance Lineman Tools & Equipment  
Catalog # [PSC6003499](#)

5H All-Angle Ground Clamp with eye screw, ASTM Grade 5H, threaded ferrule hole



### Features

- Grade 5H Rated
- Rated 47kA with X/R = 30
- First cycle current peak = 127 kA
- Last cycle current peak = 70 kA
- Test duration = 15 cycles

### General

|                                     |              |
|-------------------------------------|--------------|
| Eye Screw/T-Handle                  | 480 in-lb    |
| Installation Torque (in-lb)         |              |
| Ferrule Installation Torque (in-lb) | 250 in-lb    |
| UPC                                 | 096359659624 |

### Dimensions

|        |      |
|--------|------|
| Weight | 8 lb |
|--------|------|

### Certifications And Compliance

|                            |    |
|----------------------------|----|
| Fault Current - ASTM Grade | 5H |
|----------------------------|----|

### Product Assets

- [Catalogs - Grounding Equipment](#)
- [Literature - All Angle Clamp](#)
- [Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs](#)
- [Sales Drawings - All Angle Ground Clamp](#)