

Ground Clamp, C-Type, Type I-Class A-Grade 3H/Grade 5, 0.8in. Jaw Opening

By Chance Lineman Tools & Equipment
Catalog # [PSC6003696](#)

Ground Clamp, C-Type, Type I-Class A-Grade 3H/Grade 5, 0.8in.
Jaw Opening

Features

- C-Type Ground Clamp
- Continuous Current 300A
- Grade 3H Fault Current Rating 31kA, X/R=30
- Grade 5 Fault Current Rating 43kA for 15 cycles or 30kA for 30 cycles
- Main Line Range Max. 0.8"
- Main Line Range Min. 0.162"
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 3H
- Jaws Smooth
- Ferrule Threaded

General

Catalog Number	PSC6003696
Eye Screw/T-Handle	300 in-lb
Installation Torque (in-lb)	

Ferrule Installation Torque (in-lb)	250 in-lb
Material	Aluminum
UPC	096359719267

Dimensions

Weight	1 lb
--------	------

Logistics

Carton Quantity	30
Pallet Quantity	1440
Standard Package	1

Product Assets

[Literature - SF09197E_Compact 3H C-Clamp](#)
[Sales Drawings - SA6003696 - Compact 3H Grounding Clamp](#)
[Specifications - PSC6003696](#)

