

Ground Clamp - C-Type, Type I- Class B-Grade 5H, IEC Rating 35kA (15 Cycles), 2" Jaw Opening, Hex Screws for Strain Relief

By Chance Lineman Tools & Equipment
Catalog # [PST6003426](#)



Ground Clamp - C-Type, Type I-Class B-Grade 5H, IEC Rating 35kA (15 Cycles), 2" Jaw Opening, Hex Screws for Strain Relief

Features

- C-Type Ground Clamp
- Continuous Current 400A
- Fault Current Rating 47kA, X/R=30
- Main Line Range Max. 2" O.D. Bus
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class B, Grade 5H
- IEC Rating 35kA (15 Cycles)
- Jaws Serrated
- Ferrule Threaded - Unshrouded Only
- Hex Screws for Strain Relief

General

Catalog Number	PST6003426
Eye Screw/T-Handle	N/A
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	N/A
Handle Type	Eyescrew
Jaw Type	Serrated Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
UPC	096359453260

Dimensions

Dimensions	12.41 in x 7 in x 2.48 in
Height	2.48 in
Jaw Opening Size - Maximum	2 in
Jaw Opening Size - Minimum	.162 in
Length	12.41 in
Weight	1.75 lb
Width	7 in

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

Certifications And Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Logistics

Carton Quantity	15
Pallet Quantity	450

Product Assets

[Catalogs - Grounding Equipment](#)
[Specifications - PST6003426](#)