



# Black-Jacket Copper Grounding Cable, 4/0

By Chance Lineman Tools & Equipment  
Catalog # S3714



\*Representative Image

Copper Grounding Cable is extra-flexible for handling ease yet strong and tough for long wear. Jacketing is smooth, abrasion, weather and oilresistant in accordance with applicable ASTM Specifications, marked with AWG size approximately every 4 feet. Jackets are T-prene rubber compound with -20°F recommended low temperature. Extra-flexible cables, because of their extra-fine strands, require termination ferrules when used with grounds.

## Features

- 4/0 black-jacket copper grounding cable
- To specify cable length, please add a "P" and the length of cable in feet needed to the end of the catalog number.

## Dimensions

Weight 1.117 lb

## Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A

## Conductor Related

Conductor Size	4/0 AWG
Diameter - Cable Outside	0.87 In
Diameter - Conductor	.59 in
Nema Color	Black
Strands	2,109

## Product Assets

[Video - CHANCE Temporary Protective Grounding \(VI09071E0620\)](#)

[Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.